



Product picture shows an exemplary solution for the temperature range +2 °C to +8 °C

## DESCRIPTION

Specifically designed for door-to-door pharmaceutical distribution of smaller volumes to remote locations, OnePak ensures your products reach even the most inaccessible areas without compromising quality or efficacy. This single-use solution is ideal for regions with limited logistics services, eliminating the need for return shipping and ensuring consistent access to medicines.



## **DIMENSIONS AND WEIGHT**

External Dimens	ions (l x w x h)	Internal Dimensions <sup>1</sup> (l x w x h)		Tolerances	
[ mm ]	[inch]	[ mm ]	[inch]	[ mm ]	[inch]
480 x 460 x 385	18.9 x 18.1 x 15.2	320 x 320 x 220	12.6 x 12.6 x 8.7	± 5	± 0.2
	- w · · · 1				

Tare W	eight <sup>1</sup>	Payload <sup>1</sup> (Volume)		
[kg]	[lbs]	[L]		
12.5 ± 1	27.6 ± 2.2	23		

<sup>1</sup>including Temperature Batteries

## **TEMPERATURE BATTERY CONFIGURATION**

OneBlok	Pieces	Dimensions <sup>2</sup> (l x w x h)		Weight		Material number
ONEDIOK		[ mm ]	[inch]	[kg]	[lbs]	Haterrar Humber
34242 +22G	4	335 x 243 x 19	13.2 x 9.6 x 0.7	1.3	2.9	AK000239
34342 +22G	2	335 x 335 x 19	13.2 × 13.2 × 0.7	1.8	4	AK000237

<sup>2</sup>dimensions of empty Temperature Battery shell, variation due to PCM inside and aggregation state possible

## **PERFORMANCE** The OnePak 23 +22G is qualified in the temperature range from +15 °C to +25 °C

Temperature scenario	Duration [hrs]	Kelvin-hours <sup>3</sup>	Average ambient temperature [°C]	
ISTA 7D summer	≥ 144	≥ 1469	+30.2	
ISTA 7D winter	≥ 98	≥ -1490	+4.8	

<sup>3</sup>Detailed information about the concept of Kelvin-hours on www.kelvinhours.com

For more details, please view the qualification report. Before performing a shipment with the OnePak 23 +22G it is suggested that the user performs a validation process with the equipment available and under the conditions available. A test in worst case conditions is recommended. The box provides a very stable and well-designed system solution which has to be adapted on the particular requirements of the user.

For more information please contact support@envirotainer.com.