



Product picture shows an exemplary solution without temperature batteries

DESCRIPTION

Delivering superior performance while streamlining handling, the ProofTainer family features six sizes, accommodating from 0.5 – 2 EU or 1 - 2 US pallets. Whether you're shipping clinical trials or commercial drugs, we ensure consistent temperature control throughout your products journey. With qualified temperature ranges from -70°C to +20°C and over 120 hours of autonomy, ProofTainer provides optimal conditions for your sensitive cargo, delivering the flexibility you need for your product requirements.

DIMENSIONS AND WEIGHT

External Dimensions (l x w x h)			Internal Dimer		Tolerances		
[mm] [inch]		ch]	[mm] [inch]		[mi	m]	[inch]
1796 x 1680 x	2110 70.7 × 66	.1 x 83.1	1100 x 1720	43.3 x 67.7	, ±	8	± 0.3
Tare Weight ¹ Vo.		Volum	etric weight	Maximum Payl	oad (Weight)	Payload ¹	(Volume)
[kg]	[lbs]	[kg]	[lbs]	[kg]	[lbs]	[1	_]
1523 ± 20	3357.6 ± 44.1	1061	2339.1	1450	3196.7	16	64

¹including Temperature Batteries

TEMPERATURE BATTERY CONFIGURATION

ProofBlok	Pieces	Dimensions [mm]	s ² (l x w x h) [inch]	Weight [kg] [lbs]		Material number
27L -37G	90	470 x 275 x 32	18.5 x 10.8 x 1.3	5.3	11.7	AK000296

²dimensions of empty Temperature Battery shell, variation due to PCM inside and aggregation state possible

PERFORMANCE The ProofTainer Max -37G is qualified in the temperature range from -40 °C to -20 °C

Temperature scenario	Duration [hrs]	Kelvin-hours ³	Average ambient temperature [°C]	
controlled summer	≥ 67	≥ 3698	+20.2	

³Detailed information about the concept of Kelvin-hours on www.kelvinhours.com

For more details, please view the qualification report. Before performing a shipment with the ProofTainer Max -37G it is suggested that the user performs a validation process with the equipment available and under the conditions available. A test in worst case conditions is recommended. The box provides a very stable and well-designed system solution which has to be adapted on the particular requirements of the user.

For more information please contact support@envirotainer.com.